

Filter Data Sheet

High Purity - General Grade PTFE

Hydrophobic Teflon® Membrane for Liquid and Air Applications

General Grade PTFE Cartridges are designed for multi-purpose use wherever a cost effective PTFE membrane cartridge is required. GGPTFE series cartridges are hydrophobic and resist wetting in critical air/vent applications. Priced well below special purpose PTFE membrane cartridges, General Grade PTFE cartridges are still manufactured with the same careful attention to quality and performance.

The Extended Area option (GGPTFEX) offers up to 40% more surface area. This additional area results in significant increases in flowrate and loading capacity in the same footprint.



Flow Rate vs Pressure Drop

Rating (μ)	DI Water Flow per 1 PSID (gpm/10" (25.4cm) equivalent)
0.1	1.25 (4.7 lpm)
0.2	2.8 (10.6 lpm)
0.45	5.7 (21.5 lpm)

*Data represents GGPTFE. For GGPTFEX option, multiply given flowrate by 1.4.

Typical Applications

- Aggressive Fluids
- Fermentation Feed Air
- Venting
- Photoresists
- Inert gases

Ordering Information

GGPTFE	Rating (μ)	A	Length	C	End Cap Style	O-Rings/Gaskets	-	Adders
GGPTFEX	0.1		10" (25.4 cm)		2 = DOE Flat Gasket	B = Buna		I = Stainless Steel Insert
	0.2		20" (50.8 cm)		3 = 222 w/ Fin	E = EPDM		CS = 316ss Compression Spring
	0.45		30" (76.2 cm)		4 = 222 w/ Flat Cap	S = Silicone		
			40" (101.6 cm)		6 = 226 w/ Flat Cap	V = Viton®		
					7 = 226 w/ Fin	T = Teflon® Encapsulated Viton®		
					16 = 213 Internal O-Ring	Z = Teflon® Encapsulated Silicone		

DISCLAIMER: Filtration data presented is representative of performance observed in controlled laboratory testing. It is not given as a warranty, specification or statement of fitness for use. Specific performance can vary widely depending on contaminant type, fluid properties, flow rates and environmental conditions. It is recommended that users conduct thorough qualification testing to assure the product functions as required.

Construction Materials

MembraneTeflon®
Support MediaPolypropylene
End CapsPolypropylene
Center CorePolypropylene
Outer Support CagePolypropylene
O-Rings/GasketsBuna, EPDM, Silicone, Viton®, Teflon® Encapsulated Viton®

Sanitization/Sterilization

Filtered Hot Water80°C for 30 min.
Steam Sterilization121°C for 30 min., multiple cycles

Chemicals: Cartridges are chemically compatible with most chemicals and sanitizing agents.

Note: Stainless steel insert option needed for all cartridges being hot water sanitized or steam sterilized.

Dimensions

Length:
10 to 40 inches (25.4 to 101.6 cm) nominal
Outside Diameter:
2.70 inches (7.0 cm) nominal

Maximum Differential Pressures

Forward 50 PSI (3.4 bar) at 20°C
Reverse 40 PSI (2.7 bar) at 20°C

FDA Listed Materials

Manufactured from materials which are listed for food contact applications in Title 21 of the U.S. Code of Federal Regulations.

Toxicity

All components meet the specifications for biological safety per USP Class VI – 121°C for plastics.